# 中文

感谢您购买Olight LED Flashlight,在使 用前请详细阅读本说明书,本说明书话 用于S10 Baton.

### 标配清单:

手申\*1. 持绳\*1. 持环\*1. 说明书\*1.

## 产品说明及安装指示:



#### 操作说明:

1.按照图示安装电池。

- 2. 关机状态下, 按下开关按键, 在1秒内释放。 手电开启,输出记忆的亮度,再次单按开关 键,输出关闭:
- 3. 关机状态下,按住开关按键1秒以上,手 电开启月光模式:
- 4. 在月光模式下, 按下开关按键并保持1秒 以上,输出进入低亮,若持续按住按键,输 出在低-中-高-中-低顺序依次循环,释 放按键,输出亮度锁定。
- 5. 开机后、快速连按开关键两次,输出暴 公司 (1967年) (196740) (196740) (196740) (196740) (196740) (196740) (196740) (196740) (196740) (196740) (196740) (196740) (196740) (196740) (196740) (196740) (196740) (196740) (1967400) (196740) (196740) (196740) (196740) (1967400) (1967400) (1967400) (1967400) (1967400)

# 

<b>观旧学就表</b> :	
材料	铝合金,表面三级 硬质氧化
尺寸	L70.5 x D23.0 mm
重量	42g(不带电池)
LED	CREE XM-L
电池	CR123A or RCR123
反光杯	橘面杯
输出亮度及 运行时间	320流明/1.5小时 70流明/7.5小时 5流明/108小时 0.5流明/360小时 暴闪:320流明/6小时
中心光强度	1,800 cd
最大射程	85米
防水	IPX 8
抗冲击	2米

## 保修条款:


1.30天保换期:Olight手电产品自售出之日起 30天内(以购买发票或者其它有效购买单据 上的日期为准), 在正常使用情况下, 出现 产品质量问题,客户可选择更换新品及部 件,或维修服务: 2. 2年免费保修期: Olight手电产品自售出之 日起2年内(以购买发票或者其它有效购买单 据上的日期为准),用户在正常使用情况 下, 出现产品质量问题, 则享受免费维修服

3. 终身有限保修: 在超过2年免费保修时间 外, Olight将提供有偿保修, 更换配件及运输 费用由用户承担, 不另收取人工费用:

4. 电池质保: Olight为随产品提供或单独销售 的可充电电池提供1年(以购买发票或者其 它有效购买单据上的日期为准) 质保: 5. 用户保修时凭Olight《质量保证卡》及购买

有效单据与经销商联系, 由经销商对消费者 提供服务,我公司将对经销商提供服务支





# Operator's Manual

LED FLASHLIGHT


MODEL:S10 Baton CREE XM-L LED

# **ENGLISH**

Thank you for purchasing the OLIGHT S10 Baton flashlight. Please read this manual carefully before using this product.

### Package Contents: Flashlight \*1 Lanyard \*1 Flying ring \*1

## User' manual \*1 Product description:



### Operational instruction:

- 1. Please install the battery according to the diagram.
- 2. Press the switch then release within one second, the light turns on and output starts at memorized brightness level. Press the switch once again to close the output.
- 3. Keep pressing the switch more than one second, the light directly enter into moonlight from off status
- 4. Under moonlight mode, keep pressing the switch more than one second, output comes into a low brightness level, if the switch is continually pressed, the output will change as a loop "low middle - high - middle - low". The brightness will he frozen until the switch is released
- 5. To activate strobe, quickly double click the switch after the light is on, the strobe will not be memorized. Click the switch again will turn off the light. Under strobe mode, keep pressing the switch will guit strobe and back to memorized brightness level.

#### Specifications:

Material	Aluminum body with anti-scratching type III Hard Anodization
Dimension	L70.5 x D23.0 mm
Weight	42g(Without battery)
LED	CREE XM-L
Battery	CR123A or RCR123
Reflector	Orange peel
Output and Runtime	320lumens/1h30min 70lumens/7h30min 5 lumens/ 108h 0.5lumens/360h strobe: 320 lumens / 3h
Peak Beam intensity	1,800 cd
Beam Distance	85 meters
Waterproof	IPX 8
Impact resistance	2 meters

## Warranty:

other than Olight™.

Olight™ warrants its products to be free from defects in materials and workmanship. Within 30 days of receipt, any defective lights will be offered repair or replacement by the retailer where the product was purchased. Olight<sup>™</sup> will repair or replace, at its option and without charge, any product or part which is found to be defective under normal use and service within 24 months counting from the date of purchasing with proof of purchase, Such repair or replacement shall be the purchaser's sole and exclusive remedy under this warranty. This warranty does not cover normal maintenance and service and

accident, improper maintenance or repair by anyone

As to those exceed 24 months of the purchase date,

Olight will still provide with warranty service. Labor

covers parts and labor only as specified above.

user/owner, not the factory or dealer.

is free but cost of parts will be charged. This warranty

Freight and transit costs are the responsibility of the

does not apply to any products or parts which have been subject to modification, misuse, negligence,

E-mail:service@olightworld.com www.olightworld.com 深圳市欧莱特科技有限公司

OLIGHT

We Make A Difference

Olight Technology Co., Limited

Address: 2/F East, Building A. B3 Block.

Fuhai Industrial Park, Fuyong, Bao'an

District, Shenzhen, China 518103

Tel: +86-755-81452518/81452608

Fax: +86-755-81452508

地址:深圳市宝安区福永镇福海工业区 B3区A栋二楼东 电话: 0755-81452518/81452608 传真: 0755-81452508 E-mail:service@olightworld.com www.olightworld.com

www.DrMemory.com/Olight